


Power Transistors

TO-3 Case (Continued)



TYPE NO.		I _C	P _D	BV _{CBO}	BV _{CEO}	h _{FE}		@ I _C	V _{CE(SAT)}	@ I _C	f _T
NPN	PNP	(A) MAX	(W)	(V) MIN	(V) MIN	MIN	MAX	(A)	(V) MAX	(A)	(MHz) MIN
	2N6248	10	125	110	100	20	100	5.0	3.5	10	4.0
2N6249		10	175	300	200	10	50	10	1.5	10	2.5
2N6250		10	175	375	275	8.0	50	10	1.5	10	2.5
2N6251		10	175	450	350	6.0	50	10	1.5	10	2.5
2N6253		15	115	55	45	20	70	3.0	4.0	15	4.0
2N6254		15	150	100	80	20	70	5.0	4.0	15	- -
2N6282	2N6285	20	160	60	60	750	18,000	10	3.0	20	4.0
2N6283	2N6286	20	160	80	80	750	18,000	10	3.0	20	4.0
2N6284	2N6287	20	160	100	100	750	18,000	10	3.0	20	4.0
2N6306		8.0	125	500	250	15	75	8.0	5.0	8.0	5.0
2N6307		8.0	125	600	300	15	75	8.0	5.0	8.0	5.0
2N6308		8.0	125	700	350	12	60	8.0	5.0	8.0	5.0
2N6371		15	117	50	40	15	60	8.0	4.0	16	4.0
2N6383	2N6648	10	100	40	40	1,000	20,000	5.0	3.0	10	6.0
2N6384	2N6649	10	100	60	60	1,000	20,000	5.0	3.0	10	6.0
		10	100	80	80	1,000	20,000	5.0	3.0	10	6.0
	2N6469	15	125	50	40	20	150	5.0	3.5	15	4.0
2N6470		15	125	50	40	20	150	5.0	3.5	15	4.0
2N6471		15	125	70	60	20	150	5.0	3.5	15	4.0
2N6472		15	125	90	80	20	150	5.0	3.5	15	4.0
2N6542		5.0	100	650	300	7.0	35	3.0	1.0	3.0	6.0
2N6543		5.0	100	850	400	7.0	35	3.0	1.0	3.0	6.0
2N6544		8.0	125	650	300	7.0	35	5.0	1.5	8.0	6.0
2N6545		8.0	125	850	400	7.0	35	5.0	1.5	5.0	6.0
2N6546		15	175	650	300	12	60	5.0	1.5	10	6.0
2N6547		15	175	850	400	12	60	5.0	1.5	10	6.0
2N6569	2N6594	12	100	45	40	15	200	4.0	1.5	4.0	2.5
2N6576		15	120	60	60	2,000	20,000	4.0	4.0	15	6.0
2N6577		15	120	90	90	2,000	20,000	4.0	4.0	15	6.0
2N6578		15	120	120	120	2,000	20,000	4.0	4.0	15	6.0
2N6671		8.0	150	350	300	10	40	- -	2.0	8.0	15
2N6672		8.0	150	400	350	10	40	- -	2.0	8.0	15
2N6673		8.0	150	450	400	10	40	- -	2.0	8.0	15

Shaded areas indicate Darlington.

(6-December 2004)

Central
Semiconductor Corp.
www.centalsemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix " TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix " PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[2N6543 TIN/LEAD](#)