




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Technology	Electro-Mechanical	
Resonant Frequency	2,300	(Hz)
Rated Voltage	1.5	(V)
SPL @ 10cm	80	(dBA)
Tone	Single	
Mount Type	Thru Hole	
Voltage Range	1.2 ~ 3	(V)
Max Rated Current	20	(mA)
Housing Material	NORYL	
Operating Temperature	-30 ~ +70	°C
Storage Temperature	-40 ~ +85	°C
Weight	2	(g)

## Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



Electro-Mechanical Indicator

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			10/21/2013	J.S

IE122301-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[IE122301-1](#)