




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Technology	Electro-Mechanical	
Resonant Frequency	400	(Hz)
Rated Voltage	9	(V)
SPL @ 10cm	75	(dBA)
Tone	Single Tone	
Mount Type	Thru Hole	
Voltage Range	6 ~ 12	(V)
Max Rated Current	25	(mA)
Housing Material	ABS	
Operating Temperature	-10 ~ +60	°C
Storage Temperature	-20 ~ +70	°C
Weight	10	(g)

## Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



DB UNLIMITED

Electro-Mechanical Indicator

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			10/21/2013	J.S

IE220409-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[IE220409-1](#)