



Specifications			Notes	Revision History								
Description	Value	Unit		Version	Description			Date	Approved			
Technology	Piezo		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering			10/21/2013	J.S			
Resonant Frequency	3,700	(Hz)										
Rated Voltage	12	(V)										
SPL @ 10cm	100	(dBA)										
Tone	Single											
Mount Type	Flange											
Voltage Range	3 ~ 16	(V)										
Max Rated Current	8	(mA)										
Housing Material	ABS											
Operating Temperature	-20 ~ +60	°C										
Storage Temperature	-20 ~ +60	°C										
Weight	5	(g)										
 DB UNLIMITED						Drawn by		Date	Checked by	Date	Approved by	Date
						A.B.		10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
						IP233712-1						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[IP233712-1](#)