





DB UNLIMITED

Part Number:	1	
	DRAWN	8/9/2021
	CJ	
Description:	CHECKED	8/10/2021
	L.L.	
	APPROVED	8/10/2021
	J.S.	
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Min. Sound Pressure Level	100	dB (@ 10cm)				
Tone	Single					
Resonant Frequency	3,000	Hz				
Rated Voltage	12	V				
Voltage Range	3 ~ 20	V				
Max. Rated Current	10	mA				
Storage Temperature	-30 ~ +70	°C				
Operating Temperature	-20 ~ +60	°C				
Connection Method	PC Pin					
Mount Type	Thru Hole					
Housing Material	ABS					
Weight	7	g				

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/21/2013	J.S.
1	Updated drawing, temperature and weight	8/10/2021	L.L.

NOTES			
1) All dimensions are in mm unless otherwise noted			
2) All tolerances are ± 0.5 mm unless otherwise noted			
3) All parts meet RoHS			
4) Subject to change or redrawn without notice			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[IP303012-1](#)