

S	Specifications	•	Notes		Revision History					
Description	Value	Unit			Version	Description		Date	Approved	
Technology	Piezo		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,800	(Hz)	2) All parts meet RoHS							
Rated Voltage	12	(V)								
SPL @ 10cm	106	(dBA)								
Tone	Single									
Mount Type	Flange Mount									
Voltage Range	3~30	(V)								
Max Rated Current	10	(mA)								
Housing Material	ABS				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-30 ~ +80	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-40 ~ +85	°C		Piezo Indicator		IP412812-2				
Weight	15	(g)		Fiezo illuicator						!

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

DB Unlimited: