





DB UNLIMITED

Part Number:	DRAWN	4/25/2017
	CJ	
	CHECKED	4/28/2017
Description:	P.D.	4/28/2017
	APPROVED	
	C.E.	
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Directivity	Noise Cancelling					
Sensitivity	-54 ± 3	dB				
Frequency Range	100 ~ 10,000	Hz				
Rated Voltage	2	V	REV	DESCRIPTION	DATE	APPROVED
Voltage Range	1 ~ 10	V		Released from Engineering	2/9/2014	J.S.
Output Impedance	2,200	Ω	1	Updated to new template	4/28/2017	C.E.
Max. Rated Current	0.5	mA	2	Updated description	6/1/2021	P.D.
Storage Temperature	-20 ~ +60	°C				
Operating Temperature	-10 ~ +50	°C				
Signal to Noise Ratio	>55	dB				
Mount Type	Flush Mount					
Connection Method	Solder Pads					

REVISION HISTORY

NOTES

- 1) All dimensions are in mm unless otherwise noted
- 2) All tolerances are ± 0.5 mm unless otherwise noted
- 3) All parts meet RoHS
- 4) Subject to change or redrawn without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MN045302-1](#)