





DB UNLIMITED

Part Number: MO093803-3 Description: Electret Condenser Microphone	DRAWN CJ	8/30/2018
	CHECKED C.H.	9/4/2018
	APPROVED C.E.	9/4/2018
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Directivity	Omnidirectional					
Sensitivity	-38	dB				
Frequency Range	50 ~ 16,000	Hz				
Rated Voltage	3	V				
Voltage Range	3 ~ 10	V				
Output Impedance	2,200	Ω				
Max. Rated Current	0.5	mA				
Storage Temperature	-25 ~ +70	°C				
Operating Temperature	-20 ~ +60	°C				
Signal to Noise Ratio	60	dB				
Mount Type	Flush Mount					
Connection Method	Solder Pads					

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/21/2013	J.S.
1	Updated drawing to new template	9/4/2018	C.E.

NOTES	
1) All dimensions are in mm unless otherwise noted	
2) All tolerances are ± 0.5 mm unless otherwise noted	
3) All parts meet RoHS	
4) Subject to change or redrawn without notice	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MO093803-3](#)