




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Directivity	Omnidirectional	
Technology	Electret Condenser	
Sensitivity	-40	(dB)
Frequency Range	50 ~ 16,000	(Hz)
Rated Voltage	1.5	(V)
Impedance	2,200	(Ohm)
Connection Method	Solder Pads	
Voltage Range	1 ~ 10	(V)
Max Rated Current	0.5	(mA)
Min. Signal to Noise Ratio	>60	(dB)
Operating Temperature	-10 ~ +50	°C
Storage Temperature	-20 ~ +60	°C

## Notes

- 1) All dimensions are in mm unless otherwise noted  
 2) All parts meet RoHS



DB UNLIMITED

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			2/9/2014	J.S.
Drawn by	Date	Checked by	Date	Approved by	Date
G.W.	10/31/2013	C.E.	1/16/2014	J.S.	2/9/2014

Electret Condenser Microphone

MO094001-2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MO094001-2](#)