



TOP VIEW



SIDE VIEW



Specifications

Description	Value	Unit
Shape	Round	
Resonant Frequency	420	(Hz)
Frequency Range	420 ~ 12,000	(Hz)
SPL @ 10cm	85	(dBA)
Impedance	50	(Ohm)
Cone Material	Mylar	
Nominal Power	1.0	(W)
Max Power	1.2	(W)
Mount Type	Flush Mount	
Operating Temperature	-40 ~ +66	°C
Storage Temperature	-40 ~ +66	°C
Weight	13	(g)

Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



DB UNLIMITED

Dynamic Speaker

Revision History

Version	Description			Date	Approved
1	Released from Engineering			2/5/2014	J.S.
Drawn by	Date	Checked by	Date	Approved by	Date
G.W.	1/27/2014	C.E.	1/28/2014	J.S.	2/5/2014

SM570450-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SM570450-1](#)