



TOP VIEW



SIDE VIEW



## Specifications

Description	Value	Unit
Shape	Round	
Resonant Frequency	420	(Hz)
Frequency Range	420 ~ 5,000	(Hz)
SPL @ 10cm	101	(dBA)
Impedance	8	(Ohm)
Cone Material	Paper	
Nominal Power	0.5	(W)
Max Power	0.8	(W)
Mount Type	Flush Mount	
Operating Temperature	-30 ~ +60	°C
Storage Temperature	-30 ~ +60	°C
Weight	45	(g)

## Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



DB UNLIMITED

Dynamic Speaker

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			2/5/2014	J.S.
Drawn by	Date	Checked by	Date	Approved by	Date
G.W.	1/27/2014	C.E.	2/5/2014	J.S.	2/5/2014

SP570408-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SP570408-1](#)