


Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description		Date	Approved	
Shape	Rectangle		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		2/5/2014	J.S.	
Resonant Frequency	550	(Hz)							
Frequency Range	550 ~ 8,000	(Hz)							
SPL @ 10cm	98	(dBA)							
Impedance	8	(Ohm)							
Cone Material	Paper								
Nominal Power	3	(W)							
Max Power	5	(W)							
Mount Type	Frame Mount								
Operating Temperature	-20 ~ +60	°C							
Storage Temperature	-20 ~ +60	°C	 DB UNLIMITED	Drawn by	Date	Checked by	Date	Approved by	Date
Weight	17	(g)		G.W.	1/27/2014	C.E.	1/29/2014	J.S.	2/5/2014
				Dynamic Speaker			SP700508-1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SP700508-1](#)