





DB UNLIMITED

|  |                  |            |
|--|------------------|------------|
| Part Number:<br><br>SW330204-1   | DRAWN<br>CJ      | 11/20/2018 |
|  | CHECKED<br>C.H.  | 11/29/2018 |
|  | APPROVED<br>C.E. | 11/29/2018 |
| Description:<br>Waterproof Dynamic Speaker   |                  |            |
| This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at <a href="http://www.dbunlimitedco.com">www.dbunlimitedco.com</a> |                  |            |


Top View



Side View



Bottom View



| Items                 | Specifications | Conditions        |  |  |  |  |
|-----------------------|----------------|-------------------|--|--|--|--|
| Sound Pressure Level  | 99             | dB (@ 10cm), Avg. |  |  |  |  |
| Resonant Frequency    | 280            | Hz                |  |  |  |  |
| Frequency Range       | 280 ~ 20,000   | Hz                |  |  |  |  |
| Nominal Power         | 2.5            | W                 |  |  |  |  |
| Max. Power            | 3              | W                 |  |  |  |  |
| Impedance             | 4              | Ω                 |  |  |  |  |
| Cone Material         | Aluminum       |                   |  |  |  |  |
| Mount Type            | Flush Mount    |                   |  |  |  |  |
| IP Rating             | IP67           |                   |  |  |  |  |
| Storage Temperature   | -20 ~ +55      | °C                |  |  |  |  |
| Operating Temperature | -20 ~ +55      | °C                |  |  |  |  |
| Weight                | 34             | g                 |  |  |  |  |

| REVISION HISTORY |                           |            |          |
|------------------|---------------------------|------------|----------|
| REV              | DESCRIPTION               | DATE       | APPROVED |
|                  | Released from Engineering | 11/29/2018 | C.E.     |

| NOTES   |  |
|---|--|
| 1) All dimensions are in mm unless otherwise noted    |  |
| 2) All tolerances are ± 0.5 mm unless otherwise noted |  |
| 3) All parts meet RoHS                                |  |
| 4) Subject to change or redrawn without notice        |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SW330204-1](#)