



Part Number: SW400204-1	DRAWN CJ	10/24/2018
	CHECKED C.H.	10/25/2018
	APPROVED C.E.	10/25/2018
Description: Waterproof Dynamic Speaker		
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions
Sound Pressure Level	99	dB (@ 10cm), Avg.
Resonant Frequency	220	Hz
Frequency Range	220 ~ 20,000	Hz
Nominal Power	3	W
Max. Power	4	W
Impedance	4	Ω
Cone Material	PU + Aluminum	
Mount Type	Flush Mount	
IP Rating	IP67	
Storage Temperature	-20 ~ +55	°C
Operating Temperature	-20 ~ +55	°C
Weight	18.5	g

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/25/2018	C.E.
NOTES			
1) All dimensions are in mm unless otherwise noted			
2) All tolerances are ± 0.5 mm unless otherwise noted			
3) All parts meet RoHS			
4) Subject to change or redrawn without notice			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SW400204-1](#)