





DB UNLIMITED

Part Number:	1	
	DRAWN	2/15/2019
Description:	CJ	
	CHECKED	2/18/2019
	C.H.	
Electro-Mechanical Transducer	APPROVED	2/18/2019
	C.E.	
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Min. Sound Pressure Level	80	dB (@ 10cm)				
Resonant Frequency	2,048	Hz				
Rated Voltage	1.5	V				
Voltage Range	1 ~ 5	V				
Coil Resistance	50 ± 7.5	Ω				
Max. Rated Current	20	mA				
Storage Temperature	-40 ~ +85	°C				
Operating Temperature	-30 ~ +70	°C				
Connection Method	PC Pins					
Mount Type	Thru-Hole					
Housing Material	Noryl					
Weight	2	g				

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/21/2013	J.S.
1	Updated drawing to new template, temps	2/18/2019	C.E.

NOTES	
1) All dimensions are in mm unless otherwise noted	
2) All tolerances are ± 0.5 mm unless otherwise noted	
3) All parts meet RoHS	
4) Subject to change or redrawn without notice	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE122001-4](#)