




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Technology	Electro-Mechanical	
Resonant Frequency	2,048	(Hz)
Rated Voltage	6	(V)
SPL @ 10cm	85	(dBA)
Coil Resistance	50	(ohm)
Mount Type	Thru Hole	
Voltage Range	3 ~ 8	(V)
Max Rated Current	45	(mA)
Housing Material	NORYL	
Operating Temperature	-25 ~ +70	°C
Storage Temperature	-30 ~ +80	°C
Weight	7	(g)

## Notes

- 1) All dimensions are in mm unless otherwise noted  
2) All parts meet RoHS



DB UNLIMITED

Electro-Mechanical Transducer

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			10/21/2013	J.S
					</

TE162006-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE162006-1](#)