





Part Number:	SM180808-5	
	DRAWN	6/8/2017
	CJ	
Description:	CHECKED	10/2/2017
	P.D.	
	APPROVED	10/2/2017
Dynamic Speaker		C.E.
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at <a href="http://www.dbunlimitedco.com">www.dbunlimitedco.com</a>		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Sound Pressure Level	94	dB (@ 10cm)				
Resonant Frequency	850	Hz				
Frequency Range	850 ~ 10,000	Hz				
Nominal Power	1	W				
Max. Power	1.3	W				
Impedance	8	Ω				
Cone Material	Polymer					
Mount Type	Flush Mount					
Storage Temperature	-40 ~ +85	°C				
Operating Temperature	-30 ~ +70	°C				
Weight	2.25	g				

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/2/2017	C.E.
1	Updated drawing, specs	4/11/2018	C.E.

NOTES	
1) All dimensions are in mm unless otherwise noted	
2) All tolerances are ± 0.2 mm unless otherwise noted	
3) All parts meet RoHS	
4) Subject to change or redrawn without notice	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[SM180808-5](#)