


## **Common Mode Choke**

**TCK-122** 


Order Code	TCK-122
Inductance (each winding)	<b>5 μH ±40%</b> (at 10 kHz / 50 mV)
Impedance (DCR)	120 mΩ max.
Rated Current	1.5 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions




## Impedance Curve



## **Outline Dimensions**



All specifications valid at +25°C, unless otherwise stated.



Specifications can be changed without notice.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

TCK-122