




Order Code	TCK-138
Inductance (each winding)	16.1 μ H \pm 25% (at 100 kHz / 1 V)
Impedance (DCR)	11 m Ω max.
Rated Current	1.44 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions




Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	6.5 \pm 0.3
B	6.0 \pm 0.2
C	4.5 max.
D	4.3
E	7.7
F	0.91
G	3.0



All specifications valid at +25°C, unless otherwise stated.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TCK-138](#)