

Sealed Foam Swabs

Product# 41050, 41050I, 43170, 44070, 48040, 49280

Product Description

Coventry™ Sealed Foam Swabs are constructed from reticulated 100 pores per inch medical grade foam which features the best open cell structure, providing excellent particle entrapment characteristics. The foam is thermally bonded to the swab handle without using adhesives. These swabs are the most economical and are ideal for general applications.

- Traps surface particles while cleaning
- High solvent capacity; holds solvent well
- Fiberless construction does not generate loose fibers or particles
- No adhesives or binders are used in the construction
- Economical for high quantity applications
- Available Aqua-Prime™ processed

Typical Applications

Coventry™ Sealed Foam Swabs can be used to:


- Clean excess adhesives after gluing
- Remove contamination from disk drives
- Micro mechanical cleaning
- Maintenance and care of fax machines
- VCR's, PC's, printers, and copiers
- Remove flux residue from printed circuit boards
- Good for general purpose cleaning

Compatibility

Foam Heads are compatible with most common solvents such as isopropyl alcohol, and methanol. Not recommended for use with ketones such as acetone or methyl ethyl ketone.

Wood Handles are generally compatible with all solvents except with dilute or weak acids.

Polypropylene Handles are generally compatible with all common solvents including most dilute or weak acids.



Availability

41050 2.80 " (7.1 cm) Polypropylene Handle
0.14" (3.56 mm) Foam Head, 500/ bag

41050I Cleaned using Aqua-Prime™ process

43170 6.0 " (15.24 cm) Wood, Foam Over Cotton
0.35" (8.8 mm) Head, 500/ bag





44070 3.2 " (8.0 cm) Polypropylene Handle
0.13" (3.3 mm) Foam Head, 500/ bag

48040 2.75 " (6.8 cm) Polypropylene Flexible Tip
0.12" (3.0 mm) Foam Head, 500/ bag

49280 6.5 " (16.4 cm) Polypropylene Flexible Tip
0.19" (4.7 mm) Foam Head, 500/ bag


Sealed Foam Swabs

Product# 41050, 41050I, 43170, 44070, 48040, 49280



Sealed Foam Swabs

Product# 41050, 41050I, 43170, 44070, 48040, 49280



Sealed Foam Swabs Test Data

Head Material	Sealed Foam			
Swabs:	41050	41050I	44070	48040
Particle Counts:				
0.5 - 1 um	571	484	1,867	797
1.0 - 2 um	96	63	336	230
2.0 - 5 um	37	18	71	66
5.0 - 10 um	31	13	31	24
10 - 25 um	19	8	15	11
Over 25 um	9	1	2	2
TOTAL	762	586	2,322	1,130
NVR (ug/swab)	none detected	none detected		none detected
Chlorides (ug/swab)	none detected	none detected	0.21	none detected

The swabs were tested by Particle Measurement Technology. All the swabs tests were done using the recommended practices of the Institute of Environmental Science, Swabs and Wipes Working Group.

Test data not available for 43170 and 49280.

Technical and Application Assistance

Chemtronics provides a technical hotline to answer your technical and application related questions. The toll free number is: 1-800-TECH-401

Note:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. CHEMTRONICS does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Chemtronics® is a registered trademark of Chemtronics. All rights reserved. Coventry™ and Econowipes™ are trademarks of Chemtronics. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chemtronics:](#)

[43170](#) [49280](#)