




UL1007 22-24AWG 颜色：黑、紅 各一PCS。
一端打（杜邦2.54）端子，另一端紅色鉅100Ω電阻再打端子。

ELECTRICAL PROPERTIES:

1. 100% OPEN SHORT MIS-WIRE TEST
2. Conduction Resistance: 2 ohm max
3. Insulation resistance: 5Mega ohm MIN
4. Hi-Pot: 300V DC/10ms

5	TUBE: 4Φ 55mm X 2	2	pcs
4	Resistor: 100Ω 1/4W ± 1%	1	PCS
3	HOUSING: DP 2.54mm-1PIN+2.54mm Terminals	1	SET
2	HOUSING: DP 2.54mm-2PIN+2.54mm Terminals	1	SET
1	WIRW: UL1007 24# RED & BLK	1	pcs
NO.	DESCRIPTION	Q'TY	UNITS

Pin Assignment

COM1 COM2

1. BLK ————— BLK

2. RED ————— RED/Resistor

Tolerance:	Approved by: WXR	SMOOTH CABLE SMOOTH CORD & CONNECTOR CO., LTD. SMOOTH	
X. ±	Checked by:		
.X ±	Drawn by: CDJ	customer p/n: Resistor/2.54	
.XX ±	Date: 2016.08.26	Smooth p/n:	
.XXX ±	Scale: Unit: None m/m	Description:	
X' ±		DWG NO:	
.X' ±		SHEET: 1/1	
Specification Use Only		REV: A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Digilent:

240-116