

DMC837 GENERAL PURPOSE AF8 (M22520/1-01) STARTER TOOL KIT



**DMC837
AF8 STARTER TOOL KIT**







This "Starter Kit" is an excellent training aide for familiarizing students and beginning technicians on the proper use of the AF8 (M22520/1-01) crimp tool.

The DMC AF8, qualified to MIL-DTL-22520/1*, has virtually limitless applications within the specified wire range of 12 through 26 AWG. The adjustable head (P/N UH2-5) is ideally suited for lab work and prototype production applications. This head is attached simply by orienting the head in the keyed position, and by tightening the hex socket screws provided as part of the head. The selected contact is inserted through the entry hole on the opposite side of the tool frame from the

head. The height adjusting screw is then rotated until the contact is in the proper position for crimping. The screw can be secured with the locknut provided. Some testing will be necessary to determine the optimum selector setting for your contact/wire combination.

In addition, the DMC837 kit contains illustrated operating instructions for all the tooling included.

DMC837 TOOL AND ACCESSORY LIST

	1	Crimp Tool
	1	Universal Head
	3	Metal Insertion Tools
	3	Metal Removal Tools
	9	Plastic Installing/Removal Tools
	1	9/64" Hex Wrench
	1	Combo Cutter, Stripper, Crimper Tool

TOOL KIT CONFIGURATION

Type of Case	Portable
Number of Cases	1
Color	Grey
Type of Construction	Steel/Aluminum
Application	Contact Insertion Removal
Type of Inserts	Unicellular Polyethylene Foam with Die Cut Tool Cavities

DMC837

DMC **DANIELS
MANUFACTURING
CORPORATION**®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Daniels Manufacturing:](#)

[DMC837](#)