

UPD78F1503AGC-UEU-AX

User's Manual: Hardware

[Overview](#)[Design Support](#)[Documentation](#)[Sample Code](#)[Software & Tools](#)[Ordering](#)

PARAMETRICS

Parameters	UPD78F1503AGC-UEU-AX
Package	
Pin Count	100
Package Type	LFQFP
Memory	
Program memory	64 KB Flash memory
RAM	4 KB
CPU (Bit, Clock, DMA, External Bus etc)	
CPU	78K0R (16-bit)
Max. Frequency	20 MHz
Sub-Clock (32.768 kHz)	YES
On-chip Oscillator Freq.	20, 8, 1 MHz
Power-On Reset	YES
Low Voltage Detection	YES
DMA Remarks	DMAC x 2 ch
External Interrupt Pins	12
I/O Ports	65
Timers	
16-bit Timers	12 ch
Watchdog Timers	1 ch
PWM Output	7
Analog	
A/D Converters	12-bit x 12 ch
D/A Converters	12-bit x 2 ch
Interfaces	
CSIs	3 ch
UARTs	4 ch
I2Cs	3 ch
LIN	1 ch
Display Functions	
LCD Remarks	seg=36, com=8
Operating Conditions	
Operating Voltage	1.8 to 5.5 V
Operating Temperature	-40 to 85 °C (Ambient Temperature)
Remarks	
Remarks	100-pin 16-bit single-chip microcontroller (78K0R/LG3)

[View Less](#)

Need More Help?

- [Contact Us](#)
- [Website Feedback](#)
- [Forums](#)
- [Videos](#)
- [Knowledgebase](#)

About Renesas

- [News](#)
- [Investors](#)
- [Careers](#)

Follow Us

- Facebook
- YouTube
- Twitter
- LinkedIn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renesas Electronics:](#)

[UPD78F1503AGC-UEU-AX](#)