


Sehr kleine 13 mm (0,5") Hochtonkalotte mit Polycarbonat-Membran, ferrofluidge-
kühlter Schwingspule und sehr linearem Frequenzgang. Spritzige Höhen, hervorragendes
Rundstrahlverhalten. Für den Einsatz in 2- oder 3-Wege-Systemen kleiner und mittlerer Leistung
oder als Zusatzhochtöner; Einbau- oder Aufbaumontage möglich, insbesondere dort, wo wenig
Platz zur Verfügung steht (z. B. Spiegeldreieck, Türgriff).

Zubehör: Inklusive Montagering zum Einbau und Anschlusskabel.

Very compact 13 mm (0.5") ferro-fluid cooled tweeter with a polycarbonate cone, featuring an
absolutely linear frequency response. Crisp high-range reproduction and excellent omnidirectional
sound distribution. Tweeter in low to medium-output 2- or 3-way systems or as an additional tweeter.
Can be surface or flush mounted. Especially suitable for mounting in confined spaces (e.g. mirror
vicinity and door handles).

Accessories: Mounting ring and connecting cables included.





Technische Daten / Technical Data

Nennbelastbarkeit	60 ¹ W
Rated power	
Impedanz	4 Ω
Impedance	
Übertragungsbereich (–10 dB)	1700–22000 Hz
Frequency response (–10 dB)	
Mittlerer Schalldruckpegel	86 dB (1 W/1 m)
Mean sound pressure level	
Resonanzfrequenz	2400 Hz
Resonant frequency	
Schwingspulendurchmesser	13 mm Ø
Voice coil diameter	
Wickelhöhe	1,5 mm
Height of winding	
Schallwandöffnung	33,5 mm Ø
Cut-out diameter	
Gewicht netto	26 g
Net weight	

¹ über Frequenzweiche 12 dB/Okt. ab mind. 6000 Hz /
via crossover network 12 dB/Oct. as of 6000 Hz

CP 13 - 4 Ohm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Visaton:](#)

[4454](#)