

Ferrite coil with tinned wire ends. Very high power handling, low loss due to the low internal resistance.



Art. No.	Article	Technical Data	
3601	LR 1,5 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,32 mm
		Internal resistance	0,17 Ohm
		Saturation current	13,4 A
3605	LR 3,3 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,32 mm
		Internal resistance	0,25 Ohm
		Saturation current	12,1 A
3607	LR 3,9 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,32 mm
		Internal resistance	0,27 Ohm
		Saturation current	11,5 A
3608	LR 4,7 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,18 mm
		Internal resistance	0,28 Ohm
		Saturation current	9,3 A
3610	LR 6,8 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,18 mm
		Internal resistance	0,35 Ohm
		Saturation current	7,4 A
3613	LR 10,0 mH	Height	36 mm
		Diameter	56 mm
		Wire diameter	1,12 mm
		Internal resistance	0,55 Ohm
		Saturation current	5,2 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Visaton:

[3601](#) [3605](#) [3607](#) [3608](#) [3610](#) [3613](#)