

CT2060

Banana Plug Test Lead, PVC

4mm Straight Banana Plug to Straight Banana Plug Test Lead

Description

4mm banana plugs on both ends. With 18 AWG (0.75 mm²)

PVC jacketed lead wire.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 V AC / 70 V DC
Voltage, Max	1,200 V AC/DC
Current, Max	12 A
Jacket Material	PVC
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2060-100-5](#) [CT2060-100-9](#) [CT2060-10-2](#) [CT2060-10-4](#) [CT2060-10-5](#) [CT2060-10-6](#) [CT2060-50-5](#) [CT2060-50-6](#)
[CT2060-50-9](#) [CT2060-100-6](#) [CT2060-10-0](#) [CT2060-100-4](#) [CT2060-200-9](#) [CT2060-25-4](#) [CT2060-25-5](#) [CT2060-25-](#)
[6](#) [CT2060-25-9](#) [CT2060-50-4](#) [CT2060-150-9](#) [CT2060-200-0](#) [CT2060-200-2](#) [CT2060-200-4](#) [CT2060-200-5](#) [CT2060-](#)
[200-6](#) [CT2060-10-9](#) [CT2060-150-0](#) [CT2060-150-2](#) [CT2060-150-4](#) [CT2060-150-5](#) [CT2060-150-6](#)