

CT2062

Banana Plug Test Lead, Silicone

4mm Straight Banana Plug to Straight Banana Plug Test Lead

Description

Standard 4mm straight banana plugs on both ends. With 18 AWG (0.75 square millimeters) silicone jacketed lead wire.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 V AC / 70 V DC
Voltage, Max	1,200 V AC/DC
Current, Max	12 A
Resistance, Max	55 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2062-10-0](#) [CT2062-10-5](#) [CT2062-10-6](#) [CT2062-10-9](#) [CT2062-100-4](#) [CT2062-100-5](#) [CT2062-10-2](#) [CT2062-10-4](#)
[CT2062-25-6](#) [CT2062-25-9](#) [CT2062-50-4](#) [CT2062-50-5](#) [CT2062-50-6](#) [CT2062-50-9](#) [CT2062-200-4](#) [CT2062-200-5](#)
[CT2062-200-6](#) [CT2062-200-9](#) [CT2062-25-4](#) [CT2062-25-5](#) [CT2062-100-6](#) [CT2062-100-9](#) [CT2062-150-4](#) [CT2062-150-5](#) [CT2062-150-6](#) [CT2062-150-9](#)