


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.


1. SAFETY SOCKET w/ \varnothing .080 (\varnothing 2.0) SOLDER FORK.
2. SPECIFICATIONS:
INSULATOR: POLYAMIDE
CONTACT: BRASS, NICKEL PLATED
LOCKING NUT: BRASS, NICKEL PLATED
3. RATING:
VOLTAGE: 1,000V CATIII P2 (IEC61010-1)
CURRENT: 25A MAX.
RESISTANCE: $<5\text{m}\Omega$.
TEMPERATURE: -20°C TO $+80^{\circ}\text{C}$.
4. MOUNTING HOLE: REF. DIAGRAM
5. INSULATOR THREAD, M12 X 0.75
6. MAXIMUM PANEL THICKNESS: .40 (10.2).

PART NUMBER

CT2242-#

- COLOR: 0 – BLACK
1 – BROWN
2 – RED
3 – ORANGE
4 – YELLOW
5 – GREEN
6 – BLUE
7 – PURPLE
8 – GRAY
9 – WHITE



THIRD ANGLE PROJECTION		<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ±.005 DO NOT SCALE DRAWING</div>		CONTRACT NO.		<div>Cal Test Electronics</div> <div>22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610</div>							
				APPROVALS		DATE		<div>TITLE</div> <div>4mm SAFETY SOCKET, w/∅ .080(∅ 2mm)SOLDER FORK</div>					
				DRAWN WDH		7/12/99							
				CHECKED									
				ENGR.									
MATERIAL		DESIGN ACTIVITY				SIZE A		CAGE CODE 43F45		DWG. NO. P224200		REV. A	
FINISH						SCALE 1:1						SHEET 1 OF 1	
NEXT ASSY													
USED ON													
APPLICATION													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2242-0](#) [CT2242-2](#) [CT2242-6](#) [CT2242-5](#) [CT2242-7](#) [CT2242-8](#) [CT2242-9](#) [CT2242-4](#)