



THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

1. INSULATED BNC MALE WITH 4mm SAFETY JACKS.
APPLICATION: ADAPTS BNC FEMALE CONNECTOR TO 4mm SHEATHED JACKS TO ACCEPT SHEATH BANANA PLUGS.
UPGRADES BNC TO IEC SPECIFICATIONS.
2. SPECIFICATIONS:
INSULATOR: POLYAMIDE (NYLON), GREY
JACK CONTACTS: BRASS, NICKEL PLATED
BNC(m): BRASS. CENTER CONTACT, GOLD PLATED.
3. RATING:
VOLTAGE: 500V CATI OR 150V CATIII P2 (IEC61010-1)
CURRENT: 3A MAX.
RESISTANCE: <0.8mΩ.
TEMPERATURE: -20° C TO +80° C.

PART NUMBER
CT2412

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/12/99	



SCHEMATIC

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS .XX ± .02 DECIMALS ± 1/32 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610	
		MATERIAL		APPROVALS		TITLE	
		FINISH		DATE		INSULATED BNC(m) w/4mm SHEATHED SAFETY JACKS	
NEXT ASSY		USED ON		DRAWN WDH		SIZE A	
APPLICATION				CHECKED		CAGE CODE 43F45	
				ENGR.		DWG. NO. P241200	
				DESIGN ACTIVITY		REV. —	
						SCALE 1:1	
						SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2412](#) [CT2702A](#) [CT3655](#) [CT3387](#) [CT2701A](#) [CT3956](#) [CT3340](#) [CT2941](#) [CT3161-0](#) [CT3390](#) [CT2410](#) [CT3378](#)
[CT3197](#) [CT2986](#) [CT3392](#) [CT3349](#) [CT3314](#) [CT3321](#) [CT2985](#) [CT3888](#) [CT2771](#) [CT3316](#) [CT3379](#) [CT2763](#)
[CT3391](#) [CT3389](#) [CT3435](#) [CT3889](#) [CT2619](#) [CT3380](#) [CT3322](#) [CT3348](#) [CT3320](#) [CT2762](#) [CT3161-2](#) [CT3317](#)
[CT3347](#) [CT3346](#) [CT2940](#) [CT3315](#) [CT2939](#)