

CT2485

Banana Plug Test Lead Set

Pair, Black & Red, 4mm Straight Sheathed Banana Plug to...

Description

Test lead pair, Black and Red. Straight to straight sheathed banana plugs for interconnecting instruments, probes and clips. Test Lead Wire is Silicone jacketed, 0.75 mm² (18 AWG), length 150 cm (60").

- Rated to 1,000 V CAT IV
- Black and Red colors
- Silicone Jacket
- Safety plug tips (grey)



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT IV
Current, Max	12 A
Resistance, Max	45 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Length	150 cm (60")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2485](#)