

CT2661

DMM Probe Spade Lug Adapter

Pair of multimeter probe 6/4 mm Spade Lugs to 4mm...

Description

2 pieces of 6/4 mm Spade Lug to 4mm jack, pair Black and Red. Accepts 4 mm sheathed banana plugs. Use to connect to terminal or binding post.

- Black and Red colors
- Materials: Body: Polyamide (Nylon); Contact: Brass, Nickel Plt.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

Cal Test
ELECTRONICS 

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	30 Vac / 60 Vdc
Current Max	36A
Resistance Max	1 milliohms
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2661](#)