

# CT3130

## Banana Plug Test Lead Set

Pair, Black & Red, 4mm Straight, Banana Plug to Right-Angle...

### Description

Test lead pair, Black and Red. Most common lead for handheld DMMs. Right-Angle Banana Plug for the meter and straight banana plug for the probe or clip. With PVC jacketed wire, 1.00 mm<sup>2</sup> (17 AWG), length 100 cm (40").



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

# Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

## Specifications

<b>IEC Rating</b>	<b>1,000 V CAT III / 600 V CAT IV</b>
<b>Current, Max</b>	<b>20 A</b>
<b>Resistance, Max</b>	<b>25 milliohms</b>
<b>Jacket Material</b>	<b>PVC</b>
<b>Length</b>	<b>100 cm (40")</b>
<b>Conductor Area</b>	<b>1.00 mm<sup>2</sup></b>
<b>Wire Gauge</b>	<b>17 AWG</b>
<b>Stranding (# x dia.)</b>	<b>259 x 0.07</b>
<b>OD, mm (in)</b>	<b>3.8 mm (0.150")</b>
<b>Temperature (degrees)</b>	<b>-20 to +80C</b>
<b>RoHS (2011/65/EU)</b>	<b>Compliant</b>

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3130](#)