

CT3132

Banana Plug Test Lead Set

Pair, Black & Red, 4mm Straight Banana Plug to Right-Angle...

Description

Test lead pair, Black and Red. Common replacement test lead set for handheld DMMs. Right-Angle Banana Plug for the meter and straight banana plug for the probe or clip. With Silicone jacketed wire, 0.75 mm² (18 AWG), length 100 cm (40").



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III / 600 V CAT IV
Current, Max	12 A
Resistance, Max	30 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Length	100 cm (40")
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3132](#)