

CT3188

MiniPro Test Clip to 4mm Sheath Plug

Connect your MiniPro Test Clip to any standard DMM jack

Description

Connect your MiniPro Test Clip to any standard DMM jack.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 Vac / 70 Vdc
Current Max	6 A
Jacket Material	PVC
Conductor Area, square millimeters	0.40
Wire Gauge, AWG	21
Stranding, # x mm	104 x 0.07
OD, mm (in)	2.0mm (0.079")
Temperature (degrees)	-20 to +80 degC
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3188-10-2](#) [CT3188-10-0](#)