

Do-It-Yourself Quick Connect solderless straight banana plug Depress the spring...

Description

Do-It-Yourself Quick Connect banana plug. Just strip the wire, depress the spring loaded button, insert the wire and release. The connection is complete including a secure grip on the wire's insulation.

- Materials: Body: Polyamide (Nylon); Plug: Brass, Nickel Plt; Contact: BeCu, Nickel Plt
- Conductor Size: 2.5square millimeters (Approx. 13AWG) Max.; Jacket: 3.9mm (0.154") Max.
- RoHS Compliant.
- Available in 6 colors



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 Vac / 70 Vdc
Voltage Max	1,200 Vac/dc
Current Max	20 A
Resistance Max	10 mohm
Temperature (degrees)	-20 to +80 degC
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3249-0](#) [CT3249-5](#) [CT3249-4](#) [CT3249-9](#)