

# CT3804

## Banana Plug Test Lead

# Datasheet

4mm Right-Angle Sheath Banana Plug to Insulated Alligator Clip Test Lead,...

### Description

4mm Right-Angle Sheath Banana Plug to Insulated Alligator Clip Test Lead. Highly flexible silicone jacketed test lead wire.

- Banana Contact: BeCu, Nickel Plt.
- Alligator Clip: Steel, Nickel Plt.
- Jaws open to 0.31" (7.9 mm)
- Available in 2 standard lengths
- Available in 2 colors



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### **Specifications**

|                              |                      |
|------------------------------|----------------------|
| <b>UL Rating</b>             | 300 V CAT II         |
| <b>Current, Max</b>          | 10 A                 |
| <b>Jacket Material</b>       | Silicone             |
| <b>Conductor Area</b>        | 0.87 mm <sup>2</sup> |
| <b>Wire Gauge, AWG</b>       | 18 AWG               |
| <b>Stranding (# x dia.)</b>  | 168 x 0.07 mm        |
| <b>Jacket OD</b>             | 3.7 mm (0.146")      |
| <b>Temperature (degrees)</b> | -20 to +80C          |
| <b>RoHS (2011/65/EU)</b>     | Compliant            |

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3804-30-2](#) [CT3804-100-0](#) [CT3804-60-2](#) [CT3804-30-0](#) [CT3804-60-0](#) [CT3804-100-2](#)