

CT3805

Banana Plug Test Lead

Datasheet

Pair of 4mm Right-Angle Sheath Banana Plug to Insulated Alligator...

Description

Pair of 4mm Right-Angle Sheath Banana Plug to Insulated Alligator Clip Test Leads, Black and Red. Highly flexible silicone jacketed test lead wire.

- Banana Contact: BeCu, Nickel Plt.
- Alligator Clip: Steel, Nickel Plt.
- Jaws open to 0.31" (7.9 mm)
- Available in 3 standard lengths
- Black and Red pair



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

UL Rating	300 V CAT II
Current, Max	10 A
Jacket Material	Silicone
Conductor Area	0.87 mm ²
Wire Gauge, AWG	18 AWG
Stranding (# x dia.)	168 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3805-60](#) [CT3805-30](#) [CT3805-100](#)