

CT3809

Alligator Clip Test Lead

Datasheet

Individual color, insulated alligator clip to insulated alligator clip w/18...

Description

Individual color, standard insulated alligator clip to standard insulated alligator clip test lead. Alligator clips have insulated PVC boots. Test lead wire is 18 AWG with highly flexible silicone jacket.

Features:

- Materials:
- Body & spring: steel, nickel plated
- Insulator: PVC
- Wire: bare copper, high stranding; silicone jacket
- Jaws open to 7.9 mm (0.31")
- Available in 2 colors and 3 lengths
- IEC 61010-031 rated

Available as a black and red pair Model CT3810



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Voltage Rating	300 V CAT II
Current, Max	10 A
Jacket Material	Silicone
Wire Gauge	18 AWG (0.82 mm ²)
Stranding (# x dia.)	168 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3809-100-2](#) [CT3809-100-0](#) [CT3809-60-0](#) [CT3809-30-0](#) [CT3809-30-2](#) [CT3809-60-2](#)