

CT3982

Datasheet

Probe Lead to Shth P w/Hooks - SILIC 0.82, 120cm B/R Pair

Probe Set w/Straight 4mm Sheath Banana Plugs, plus Spring Hooks

Description

Probe set with 2mm tips and straight 4mm sheath banana plug connectors. Probe set includes spring hook adapters with snap-lock attachment. Cap on probe allows 1,000 V CAT III/600 V CAT IV rating. Silicone lead wire for high flexibility.

- IEC 61010-031 rated
- Silicone lead wires
- Tip w/o cap 2 mm (.080") x 19 mm (.75")
- Black and red pair
- Spring hook pair - rated 300 V CAT II



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III / 600 V CAT IV w/Cap
Current Max	10 A
Jacket Material	Silicone
Wire Gauge, AWG	18
Stranding, # x mm	168 x 0.07
OD, mm (in)	3.7mm (0.146")
Temperature (degrees)	-20to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3982-120](#)