

# CT3984

# Datasheet

## Probe Lead to Shth RaP - SILIC 0.82, 120cm

Individual, CAT IV DMM probe with silicone lead and right-angle...

### Description

Individual DMM probe lead with 2 mm (.080) diameter x 19 mm (0.75) probe tips. With safety caps installed, probe meets 600V CAT IV per IEC 61010-031. Remove the safety caps to access standard 2 mm tips and attach optional tip accessories that snap-lock to the probe body for secure connection.

### Features:

- Highly flexible silicone jacket lead wire
- 4 mm right-angle sheath banana plug connector
- Tip: Brass, Nickel plated
- Tip fits North American power sockets

Optional tip accessory pairs that snap-lock to the probe tips:

- CT3941 Extended Tips
- CT3943 Alligator Clips
- CT3945 Spade Lugs
- CT3947 Spring Hooks



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### **Specifications**

|                              |  |
|------------------------------|--|
| <b>IEC Rating</b>            | 1,000 V CAT III/600 V CAT IV w/Cap(CAT II w/o Cap) |
| <b>Current Max</b>           | 10 A   |
| <b>Jacket Material</b>       | Silicone   |
| <b>Wire Gauge, AWG</b>       | 18   |
| <b>Stranding</b>             | 195 x 0.07 mm                                      |
| <b>OD</b>                    | 3.7 mm (0.146")                                    |
| <b>Temperature (degrees)</b> | -20 to +80C  |
| <b>RoHS (2011/65/EU)</b>     | Compliant  |

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3984-120-2](#) [CT3984-120-0](#)