

# CT3985

# Datasheet

## Probe Lead to Shth RaP - SILIC 0.82,120cm B/R Pair

Pair, CAT IV DMM probes with silicone leads and right-angle...

### Description

Pair of DMM probes with leads, black and red, with 2 mm (.080) diameter x 19 mm (0.75) probe tips. With safety caps installed, probes meet the 600 V CAT IV per IEC 61010-031. Remove the safety caps to access standard 2 mm tips and attach optional tip accessories that snap-lock to the probe body for secure connection.

### Features:

- Pair, black and red
- Highly flexible silicone jacket lead wires
- 4 mm right-angle sheath banana plug connectors
- Tip: Brass, Nickel plated
- Tip fits North American power sockets

Excellent cross to Fluke TL75 Hard Point Test Lead Set

Optional tip accessory pairs that snap-lock to the probe tips:

- CT3941 Extended Tips
- CT3943 Alligator Clips
- CT3945 Spade Lugs
- CT3947 Spring Hooks



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### **Specifications**

<b>IEC Rating</b>	1,000 V CAT III/600 V CAT IV w/Cap(CAT II w/o Cap)
<b>Current Max</b>	10 A
<b>Jacket Material</b>	Silicone
<b>Wire Gauge, AWG</b>	18
<b>Stranding</b>	195 x 0.07 mm
<b>OD</b>	3.7 mm (0.146")
<b>Temperature (degrees)</b>	-20 to +80C
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3985-120](#)