




THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/15/2023	B. Hansen

- NOTES:
- ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.
 - ADAPTER TO MEET OR EXCEED ALL SPECIFICATIONS PER MIL-PRF-39012.
 - MATING DIMENSIONS IN ACCORDANCE WITH MIL-STD-348.
 - FREQUENCY RANGE SPECIFICATIONS ARE FOR REFERENCE AND ARE DEPENDENT ON CABLE TYPE AND OTHER APPLICATION SPECIFIC CONDITIONS.
 - MATERIAL:
 - BODY: BRASS, NICKEL PLATED
 - CENTER CONTACT: BRASS, GOLD PLATED
 - DIELECTRIC: PTFE
 - ELECTRICAL:
 - IMPEDANCE: 50Ω
 - FREQUENCY: DC - 2 GHz
 - WORKING VOLTAGE: 500 Vrms
 - MECHANICAL:
 - TEMPERATURE RANGE: -20°C TO +80°C
 - RoHS AND REACH COMPLIANT



ISOMETRIC VIEW
FULL SCALE

		CT4509		PANEL MOUNT		IN-SERIES CONNECTOR							
		MODEL NUMBER		CONFIGURATION			NOTES / REFERENCE						
		MODEL NUMBER TABLE											
THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING		PROJECT NO.		METRIC		<div>Cal TestELECTRONICS</div> <div>22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA</div>					
				APPROVALS		DATE		TITLE CONNECTOR, BNC MALE, SURFACE MOUNT w/SOLDER CUP					
				DRAWN GSG		11/2/2023							
				CHECKER B. HANSEN		11/2/2023							
				ENGR. B. HANSEN		11/2/2023							
REFERENCE		MATERIAL SEE NOTES		DESIGN ACTIVITY		SIZE B		CAGE CODE 43F45		DWG. NO. CT4509		REV. A	
		TREATMENT NONE				SCALE 2:1		SHEET 1 OF 1					
		FINISH SEE NOTES											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4509](#)