



THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/15/2023	B. Hansen

- NOTES:
- ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.
 - ADAPTER TO MEET OR EXCEED ALL SPECIFICATIONS PER MIL-PRF-39012.
 - MATING DIMENSIONS IN ACCORDANCE WITH MIL-STD-348.
 - FREQUENCY RANGE SPECIFICATIONS ARE FOR REFERENCE AND ARE DEPENDENT ON CABLE TYPE AND OTHER APPLICATION SPECIFIC CONDITIONS.
 - MATERIAL:
 - BODY: BRASS, NICKEL PLATED
 - CENTER CONTACT: BRASS, GOLD PLATED
 - HEX NUT: BRASS, NICKEL PLATED
 - LOCKWASHER: BRASS, NICKEL PLATED
 - DIELECTRIC: DELRIN
 - ELECTRICAL:
 - IMPEDANCE: 50Ω
 - FREQUENCY: DC - 2 GHz
 - WORKING VOLTAGE: 500 Vrms
 - MAXIMUM PANEL THICKNESS: 4.0 mm
 - MECHANICAL:
 - TEMPERATURE RANGE: -20°C TO +80°C
 - RoHS AND REACH COMPLIANT



ISOMETRIC VIEW
FULL SCALE

		CT4513		BULKHEAD MOUNT		IN-SERIES CONNECTOR									
		MODEL NUMBER		CONFIGURATION			NOTES / REFERENCE								
		MODEL NUMBER TABLE													
THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING		PROJECT NO.		METRIC		Cal Test ELECTRONICS 22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA							
				APPROVALS		DATE		TITLE ADAPTER, BNC FEMALE TO BNC FEMALE, BULKHEAD MOUNT							
				DRAWN GSG		11/7/2023									
				CHECKER B. HANSEN		11/7/2023									
REFERENCE		MATERIAL SEE NOTES		ENGR. B. HANSEN		11/7/2023		SIZE B		CAGE CODE 43F45		DWG. NO. CT4513		REV. A	
		TREATMENT NONE		DESIGN ACTIVITY				SCALE 2:1						SHEET 1 OF 1	
		FINISH SEE NOTES													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4513](#)