

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

1. DO-IT-YOURSELF (DIY) 4mm STACKING BANANA PLUG, BUTTON ATTACHMENT (SOLDERLESS).
2. SPECIFICATIONS:
INSULATOR BODY: POLYAMIDE (NYLON)
PLUG BODY: BRASS, NICKEL PLATED
CONTACT SPRING: BERYLLIUM COPPER ALLOY, NICKEL PLATED
3. RATING:
IEC: <33 V AC / <70 V DC
VOLTAGE: 1,200 V NON-HANDHELD
CURRENT: 36 A MAX.
TEMPERATURE: -20° C TO +80° C.
4. MAXIMUM WIRE SIZES:
CONDUCTOR: Ø.090 (12AWG)
INSULATION: Ø.156 (5/32")
STRIP LENGTH: .25 (6.4)


MODEL NUMBER

CT2016-#


COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

REVISIONS

REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



THIRD ANGLE PROJECTION



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
FRACTIONS DECIMALS
± 1/32 .XX ± .02
.XXX ± .005
DO NOT SCALE DRAWING

CONTRACT NO.

APPROVALS	DATE
DRAWN WDH	7/11/99
CHECKED	
ENGR.	
DESIGN ACTIVITY	

Cal Test Electronics

22820 Savi Ranch Parkway
Yorba Linda, CA 92887-4610

TITLE
**DIY 4mm STACKING PLUG,
BUTTON ATTACHMENT**

SIZE	CAGE CODE	DWG. NO.	REV.
A	43F45	P201600	A

SCALE 1:1 SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2016-0](#) [CT2016-6](#) [CT2016-4](#) [CT2016-2](#)