


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"
OD: .146±.008 (3.7 mm)
CONDUCTOR: BARE COPPER, STRANDING 195 x 0.07 mm = 0.75 mm², 18 AWG.
- RATING:
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
CURRENT: 12 A MAX.
TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



MODEL NUMBER

CT2837-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

THIRD ANGLE PROJECTION 		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
				APPROVALS		DATE			
				DRAWN WDH		7/11/99		TITLE WIRE, TEST LEAD, PVC JACKET, 0.75 mm², 18 AWG, 12 A	
				CHECKED					
		MATERIAL		ENGR.				SIZE	CAGE CODE
		FINISH		DESIGN ACTIVITY				A	43F45
NEXT ASSY		USED ON						DWG. NO.	REV.
								P283700	A
APPLICATION								SCALE	SHEET
								NONE	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2837-2-50](#) [CT2837-0-50](#) [CT2837-2-10](#) [CT2837-5-50](#) [CT2837-0-100](#) [CT2837-5-10](#) [CT2837-6-50](#) [CT2837-4-10](#)
[CT2837-4-100](#) [CT2837-9-10](#) [CT2837-0-10](#) [CT2837-6-10](#) [CT2837-2-100](#) [CT2837-6-100](#) [CT2837-5-100](#) [CT2837-4-](#)
[50](#) [CT2837-9-100](#) [CT2837-9-50](#)