


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: SILICONE. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR" OD: .154±.008 (3.9 mm)
CONDUCTOR: BARE COPPER, STRANDING 651 x 0.07 mm = 2.50 mm², 13 AWG.
- RATING:
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
CURRENT: 36 A MAX.
TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



MODEL NUMBER

CT2844-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		TITLE WIRE, TEST LEAD, SILICONE JACKET, 2.50 mm², 13 AWG, 36 A	
				DRAWN WDH		7/11/99			
				CHECKED					
		FINISH		ENGR.				SIZE	
NEXT ASSY				DESIGN ACTIVITY				CAGE CODE	
APPLICATION								DWG. NO.	
								P284400	
								REV.	
								A	
						SCALE NONE		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2844-4-100](#) [CT2844-6-50](#) [CT2844-9-50](#) [CT2844-2-100](#) [CT2844-2-50](#) [CT2844-2-10](#) [CT2844-9-100](#) [CT2844-6-100](#) [CT2844-5-100](#) [CT2844-5-50](#) [CT2844-4-10](#) [CT2844-9-10](#) [CT2844-6-10](#) [CT2844-0-50](#) [CT2844-4-50](#) [CT2844-5-10](#)