


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:  
JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"  
OD: .079±.008 (2.0 mm)  
CONDUCTOR: BARE COPPER, STRANDING 104 x 0.07 mm = 0.40 mm<sup>2</sup>, 21 AWG.
- RATING:  
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031  
CURRENT: 6 A MAX.  
TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



**MODEL NUMBER**

**CT2878-#-XXX**

COLOR: 0 - BLACK  
2 - RED  
4 - YELLOW  
5 - GREEN  
6 - BLUE  
9 - WHITE

LENGTH: 10 - 10 m PACKAGE  
50 - 50 m SPOOL  
100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING	CONTRACT NO.		<b>Cal Test Electronics</b> 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
			APPROVALS DRAWN WDH CHECKED ENGR. DESIGN ACTIVITY		DATE 7/11/99		TITLE <b>WIRE, TEST LEAD, PVC JACKET,          0.40 mm<sup>2</sup>, 21 AWG, 6 A</b>	
		MATERIAL			SIZE <b>A</b>	CAGE CODE <b>43F45</b>	DWG. NO. <b>P287800</b>	REV. A
NEXT ASSY		FINISH			SCALE NONE		SHEET 1 OF 1	
APPLICATION								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2878-8-10](#)