


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: SILICONE. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR" OD: $.106 \pm .008$ (2.7 mm)
CONDUCTOR: BARE COPPER, STRANDING 130 x 0.07 mm = 0.50 mm², 20 AWG.
- RATING:
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
CURRENT: 10 A MAX.
TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



MODEL NUMBER

CT2884-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS $\pm 1/32$.XX $\pm .02$ XXX $\pm .005$ DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		TITLE WIRE, TEST LEAD, SILICONE JACKET, 0.05 mm², 20 AWG, 10 A	
				DRAWN WDH		7/11/99			
				CHECKED					
				ENGR.					
NEXT ASSY		USED ON		DESIGN ACTIVITY					
APPLICATION									
						SIZE A		CAGE CODE 43F45	
						DWG. NO. P288400		REV. A	
						SCALE NONE		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2884-5-10](#) [CT2884-5-100](#) [CT2884-0-10](#) [CT2884-2-10](#) [CT2884-2-100](#) [CT2884-0-100](#) [CT2884-4-50](#) [CT2884-9-50](#) [CT2884-9-10](#) [CT2884-6-10](#) [CT2884-6-100](#) [CT2884-2-50](#) [CT2884-0-50](#) [CT2884-5-50](#) [CT2884-4-100](#) [CT2884-9-100](#) [CT2884-4-10](#) [CT2884-6-50](#)