


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: SILICONE. OD: .055±.008 (1.4 mm)
CONDUCTOR: BARE COPPER, STRANDING 56 x 0.07 mm = 0.22 mm², 23 AWG.
- RATING:
VOLTAGE: 1,000 V CAT III PER IEC 61010-031
CURRENT: 2 A MAX.
TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



MODEL NUMBER

CT2956-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
			APPROVALS DRAWN WDH CHECKED ENGR. DESIGN ACTIVITY		DATE 7/11/99		TITLE WIRE, TEST LEAD, SILICONE JACKET, 0.22 mm², 23 AWG, 2 A	
		MATERIAL			SIZE A	CAGE CODE 43F45	DWG. NO. P295600	REV. A
NEXT ASSY		FINISH			SCALE NONE		SHEET 1 OF 1	
APPLICATION								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2956-0-100](#) [CT2956-5-100](#) [CT2956-9-10](#) [CT2956-6-100](#) [CT2956-0-50](#) [CT2956-5-10](#) [CT2956-5-50](#) [CT2956-9-100](#) [CT2956-9-50](#) [CT2956-2-10](#) [CT2956-6-10](#) [CT2956-4-100](#) [CT2956-0-10](#) [CT2956-4-50](#) [CT2956-2-50](#) [CT2956-4-10](#) [CT2956-6-50](#) [CT2956-2-100](#)