

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WIRTTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

1. MATERIAL:
INSULATED BODY: POLYPROPYLENE (PP), 3317, UL94-HB,
COLOR: GREY.
PLUG BODY, REAR FUSE CONTACT, & BANANA JACK: BRASS,
C360, NICKEL PLATED.
BANANA PLUG CONTACT: BeCu, C170, NICKEL PLATED.
REAR CONTACT SPRING: BeCu, NICKEL PLATED.

2. SPECIFICATIONS:
RATED VOLTAGE: 1,000 V CAT IV, PER IEC/EN 61010-
031:2015_AMD1:2018
RATED CURRENT: PER FUSE, SEE PART NUMBER TABLE.
OPERATING TEMPERATURE: 0°C TO +60°C

- 3 FUSE:
FUSES MUST BE $\varnothing 6.3 \times 32$ mm, CERAMIC, TYPE FF FAST-
ACTING, 1,000 V, 50 kA IR.
• CAL TEST CT4049, SIBA 7017240, OR EQUIVALENT.
MAXIMUM FUSE CURRENT RATING: 2 A
NOTE: ADAPTER PROTECTS EQUIPMENT AGAINST SHORT-
CIRCUITS BUT NOT AGAINST OVER-CURRENTS.


WARNING: ALWAYS CHECK FOR CONTINUITY AND OPEN OR
BLOWN FUSES PRIOR TO USE.

- REPLACEMENT STEPS:
- DISCONNECT ADAPTER FROM ALL DEVICES AND LEADS.
 - UNSCREW FUSE ADAPTER BODY.
 - REMOVE AND REPLACE FUSE.
 - SCREW ADAPTER PIECES BACK TOGETHER.
 - TEST ADAPTER FOR CONTINUITY PRIOR TO USE.




- 4 ID RINGS:
ADAPTER MODEL INCLUDES REPLACEABLE COLOR ID RINGS,
MODEL CT4132-X08 -- 8 PCS., (1) EACH - BLACK, BROWN, RED,
ORANGE, YELLOW, BLUE, GREY & WHITE.
MATERIAL: SILICONE ELASTOMER.
INSTALLATION: SLIDE ID RING OVER BANANA PLUG SHEATH
AND SNAP INTO GROOVE (AS SHOWN).

5. RoHS 2 COMPLIANT; EXEMPTION ANNEX III 6(c)

6. WEIGHT:
WITHOUT FUSE: 17 g
WITH FUSE: 20 g




ISOMETRIC VIEW



CT4140A-2.0A	FUSE ADAPTER, 2.0 A FUSE	-
CT4140A-1.5A	FUSE ADAPTER, 1.5 A FUSE	-
CT4140A-1.0A	FUSE ADAPTER, 1.0 A FUSE	-
CT4140A-0.5A	FUSE ADAPTER, 0.5 A FUSE	-
CT4140A-0.0A	FUSE ADAPTER, NO FUSE	-
MODEL NUMBER	CONFIGURATION	NOTES / REFERENCE

PART NUMBER TABLE

<div>METRIC</div>	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: PER DIN ISO 2768m		PROJECT NO. C306		<div>Cal Test Electronics</div> <div>22820 Savi Ranch Parkway Yorba Linda, CA 92887</div>			
	DO NOT SCALE DRAWING		APPROVALS		DATE		TITLE <div>4 mm IN-LINE FUSE ADAPTER, IMPROVED w/ID RINGS</div>	
	MATERIAL SEE NOTES		DRAWN WDH		4/10/2019			
			CHECKER A. SCHMIDT		4/24/2019			
	THIRD ANGLE PROJECTION	TREATMENT		ENGR. B. HANSEN		4/24/2019		SIZE B
	FINISH		DESIGN ACTIVITY				CAGE CODE 43F45	
							DWG. NO. P4140A0	
								REV. A
					SCALE 1:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4140A-0.5A](#) [CT4140A-1.0A](#) [CT4140A-1.5A](#) [CT4140A-2.0A](#) [CT4140A-0.0A](#)